


Technical Specifications for Eng3's Activated Air Technology



Activated Air Devices

NanoVi™

NanoVi™ Pro

Item Number:	4600-00	4700-00
Minimum Recommended Use*:	40 Minutes, 3 x per week	20 Minutes, 3 x per week
Excitation Mode:	Constant	Constant and Pulse
Chip Card System:	no	Included
Operation Mode:		
Timer Mode without User Chip Card:	yes	yes
Timer Mode with User Chip Card:	no	yes
Eternity Mode:	no	yes
Session Mode with User Chip Card:	no	yes
Remote Controlled Illumination of Water:	16 Colors & off	16 Colors & off
	Solid, Flash, Strobe, Fade, Smooth	Solid, Flash, Strobe, Fade, Smooth
Dimensions (w x l x h):	12" x 11" x 9"	12" x 11" x 9"
Weight:	8 lb 8 oz (3.9 kg)	8 lb 8 oz (3.9 kg)
Amount of Distilled Water for Operation:	8.5 fl oz (250 ml)	8.5 fl oz (250 ml)
Display:	Touch Screen LCD, color	Touch Screen LCD, color
Volume Adjustments:	1 factory setting	8
Brightness Adjustment:	1 factory setting	8
Air Flow:	0.141 CFM (4.0 Liters per Minute)	0.141 CFM (4.0 Liters per Minute)
Check Valve:	no	yes
Drying Cycle:	no	yes
Automatic Tests:	Self Test	Self Test
Service Check:	Not Required	Not Required
Warranty:	2 Year	2 Year

*Minimum Recommended Time for Prevention Purposes

Necessary Parts – Included with Device

Glass Container:	1	1
Holder for Glass Container:	1	1
High Performance Tubing:	1 x 2 ft (0.6 m)	1 x 2 ft (0.6 m) and 1 x 4 ft (1.2 m)
Nasal cannula:	4x 1 ft (0.3 m), 4x 7 ft (2.1 m), 1x Adjustable Diffuser 7 ft (2.1 m))	10x 1 ft (0.3 m), 10 x 7 ft (2.1 m), 2x Adjustable Diffuser 7 ft (2.1 m))
Remote Control for Color Settings:	1	1
Owner Chip Card	-	1
User Chip Card	-	2
Power Supply Input / Output	100-240V AC / 12V DC, 4A	100-240V AC / 12V DC, 4A
Power Cord (US, UK or EU)	1	1

Eng3 Corporation
877.571.9206
www.eng3corp.com

Technical specifications are subject to change without notice. Not liable for misprints.
© Copyright 2010 Eng3 Corporation. All rights reserved.

rev02